

## HSM 1049 SA PET CRUSHER



**WxDxH: 792 X1585 X 2040**

**Motor 3.0 KW, for three-phase current  
3 x 400 V/50 Hz**

Sturdy and compact design · Safe crushing and compression of PET and UBCs in a single operation · Easy operation with membrane keypad · Automatic stop with LED, once collection container full · Removable collection trolley with reusable 290 litre polythene bag · Device switches off automatically. Hopper filling: 50-70 bottles (1 litre).

**Weight : 288 Kg**

**Option :**  
**HSM PET-Crusher 1049 SA**  
**Motor 1.5 KW, For Alternating Current**  
**1 x 230 V/50 Hz**